



SOUDAFOAM FIREBLOCK

Revision: 10/16/20

Page 1 of 2

Technical Data:

Base	Polyurethane
Consistency	Stable Foam
Curing System	Moisture-cure
Skin Formation (68°F/65% R.H)	7 – 8 minutes
Drying Time (68°F/65% R.H)	Dust-free after 20 – 25 minutes
Cure Rate – Straw Foam (68°F/65% R.H)	1 hour for a 1/8" bead
Cure Rate – Gun Foam (68°F/65% R.H)	30 minutes for 1/8" bead
Cure Rate – Genius Gun (68°F/65% R.H)	1 hour for a 1/8" bead
Yield – Straw Foam	3.7 gallon cured foam
Yield – Gun Foam	11 gallon cured foam
Yield – Genius Gun Foam	6.1 gallon cured foam
Yield (ASTM C-1536) – Straw Foam	1444 linear feet for a 1/4" bead
Yield (ASTM C-1536) – Gun Foam	4315 linear feet for a 1/4" bead
Yield (ASTM C-1536) – Genius Gun Foam	2407 linear feet for a 1/4" bead
Shrink	None
Post Expansion	None
Cellular Structure	70 – 80% closed cell
Color	Orange
Insulation Factor	3.9 – 4.1 for 1 inch
Water Absorption	1% Vol
Shelf Life	18 months
Application Temperature	41°F to 95°F
Service Temperature	-40°F to 194°F

Product:

SoudaFoam Fireblock is a one-component, selfexpanding, ready to use polyurethane foam with propellants, which are completely harmless to the ozone layer. SoudaFoam Fireblock is available for use with a standard straw applicator, a foam applicator gun, and our patented Genius Gun Applicator.

Characteristics:

- Permanent color
- Paintable
- Mildew resistant
- Very good adhesion on many materials
- Very easy application
- Minimal Expanding (Gun Foam)
- Will not bow or bend window and door frames (Gun Foam)

Applications:

- Installing of window and door frames
- Filling of cavities
- Sealing of openings in roof construction
- Creation of a soundproof screen
- Mounting/sealing of window and door frames
- Connecting of insulating materials and roof construction
- Improving thermal isolation in cooling systems
- Installation of air conditioners

Packaging:

Aerosol can 12 oz (Straw) Aerosol can 20 oz (Genius Gun) Aerosol can 24 oz (Gun Foam)

Remark: This information and all further technical advice are based on SOUDAL present knowledge and experience. However, SOUDAL assumes no liability for providing such information and advice including the extent to which such information and advice may relate to existing third party intellectual property rights, especially patent rights. In particular, SOUDAL disclaims all WARRANTIES EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES FOR A PARTICULAR PURPOSE OR MERCHANTABILITY, SOUDAL SHALL NOT BE RESPONSIBLE FOR CONSEQUENTIAL, INDIRECT OR INCIDENTAL DAMAGES (INCLUDING LOSS OF PROFITS) OF ANY KIND. SOUDAL reserves the right to make any changes according to technological progress or further developments.





SOUDAFOAM FIREBLOCK

Revision: 10/16/20

Shelf life:

- 18 months in unopened packaging in a cool and dry storage place at temperatures between 41°F and 77°F
- Always store can with the valve pointed upwards

Application Instructions:

Straw/Gun: Shake the aerosol can for at least 30 seconds. Fit the adapter on the valve.

Genius Gun: Shake the canister thoroughly for 30 seconds. Open the lid on the top and straighten the applicator.

All: Apply a fine water spray to the surface which needs to be clean and free of grease and dust. Turn around the canister and extrude the foam carefully by applying pressure on the trigger. Fill holes and cavities approximately 40-50% (Mega Straw and Genius Gun Max) or 65% (Gun Foam) as the foam will expand. Shake canister regularly during application. If foam is applied in several layers, moisten between each layer of foam. Fresh foam can be removed using Soudal Foam cleaner or acetone. Cured Foam can only be removed mechanically. Application temperature 41°F to 95°F. (68°F to 77°F recommended)

Genius Gun: At the end of application, close the applicator tube screwing the sealing plug onto the Max adapter and click into the holder. Close the lid. The canister can be reactivated for up to 6 weeks if resealed correctly.

Meets:

UL 723 UL 1715 NFPA 286 ASTM E814 (modified) ASTM E84

Remarks:

- Always moisten surfaces in order to improve curing and cellular structure
- Cured PU foam must be protected from UV-radiation by painting or applying a top layer of sealants (silicone, MS Polymer, etc.)
- For the filing of large volumes apply product in layers and moisten between each layer
- We recommend preliminary compatibility tests on surfaces on which PU foams have not been applied previously
- Always store canister with the valve pointed upwards.

Health- and Safety Recommendation:

- Apply the usual industrial hygiene
- Wear gloves and safety goggles
- Remove cured foam by mechanical means only, never burn away

Limited Warranty:

SOUDAL warrants product to be of good quality and will replace or, at our election, refund the purchase price of any products proved to be defective. Satisfactory results depend not only upon quality products, but also upon many factors beyond our control. Therefore, except for such replacement or refund, SOUDAL MAKES NO WARRANTY OR GUARANTEE, EXPRESSED OR IMPLIED, INCLUDING WARRANTIES OF FITNESS FOR A PARTICULAR PURPOSE OR MERCHANTABILITY, RESPECTING ITS PRODUCTS, and SOUDAL shall have no other liability with respect thereto. Any claim regarding product defect must be received in writing one (1) year from the date of shipment. No claim will be considered without such written notice or after the specified time interval. User shall determine the suitability of the products for the intended use and assume all risks and liability in connection therewith.

Remark: This information and all further technical advice are based on SOUDAL present knowledge and experience. However, SOUDAL assumes no liability for providing such information and advice including the extent to which such information and advice may relate to existing third party intellectual property rights, especially patent rights. In particular, SOUDAL disclaims all WARRANTIES EXPRESS OR INPLIED, INCLUDING THE IMPLIED WARRANTIES FOR A PARTICULAR PURPOSE OR MERCHANTABILITY. SOUDAL SHALL NOT BE RESPONSIBLE FOR CONSEQUENTIAL, INDIRECT OR INCIDENTAL DAMAGES (INCLUDING LOSS OF PROFITS) OF ANY KIND. SOUDAL reserves the right to make any changes according to technological progress or further developments.

Page 2 of 2